

WI-M-10-XX-@

(Extra Heavy-Duty 10 AWG, Silicone Jacket Test Lead Wire)



• Mueller's WI-M-10-@ is 10 AWG, 1050/0.08 stranded, tinned copper wire with highly flexible 0.197" (5mm) diameter silicone jacket.

Ratings: Current 45 Amps @ 150°C

Voltage 600V
Dielectric Strength 2 KV/Min
Spark Test 6 KV
Bend Radius 3D

Rated Temperature -40°C to 200°C

Temperature Rating FT2 UL Safety Standard UL 758

Length: The "XX" in the model number indicated length in feet.

Standard lengths: 10', 25', 30', 50', and 100'

Color: The "@" in the model number represents color.

Available colors: -0 Black, -2 Red

Mueller Electric Company 2850 Gilchrist Rd. Bld 5A Akron, OH 44305

www.muellerelectric.com

Toll Free: 800.955.2629 Phone: 330.780.2525 Fax: 330.780.2524