

Honeywell Sensing and Control

Where to buy ?

Interactive
Catalog Home

Product Family
Information

Specification
Search

Search
Help



Representative photograph,
actual product appearance may
vary.

- ▶ Dimensions
- ▶ Available Terminals
- ▶ BZ/BA Switch
Performance
Information
- ▶ Specifications

Click here for a print friendly version of this datasheet.

BZ-2RW82-A2

BZ Series Standard Basic Switch, Single Pole Double Throw Circuitry, 15 A at 125 Vac, Roller Lever Actuator, 0,97 N [3.5 oz] Maximum Operating Force, Silver Contacts, Screw Termination, CE, CSA, DEMKO, UL

Features

- Accepted world-wide standard "Large Basic" switch
- Low operating force and differential travel
- Long mechanical life up to 20,000,000 cycles at 95% survival
- Elongated mounting hole for easier, more accurate mounting
- Current rating ranges from 15 A to 25 A
- Choice of actuation, termination and operating characteristics

Typical Applications

- Irrigation systems
- Semi-trailer trucks
- Timing devices
- Office equipment
- Test instruments
- Medical/dental equipment
- HVAC equipment
- Manually operated devices
- Valves

Description

BZ/BA Series Standard Basic Switches are used for simple or precision on/off application needs.

Product Specifications

Switch Type	Standard 25,4 mm H x 17,8 mm W x 50,8 mm L [1.0 in H x 0.7 in W x 2.0 in L]
Sealed	No
Ampere Rating	15 A
Circuitry	Single Pole Double Throw (SPDT)
Actuator	Roller Lever
Termination	Screw
Operating Temperature Range	-55 °C to 85 °C [-67 °F to 185 °F]
Voltage	125 Vac

Approvals	CE, CSA, DEMKO, UL
Actuator Length	48,26 mm [1.9 in]
Contact Type	Silver
Operating Force (O.F.)	0,97 N [3.5 oz] max.
Release Force (R.F.)	0,21 N [0.75 oz] min.
Overtravel (O.T.)	3,96 mm [0.156 in] min.
Differential Travel (D.T.)	0,10 mm - 1,00 mm [0.004 in - 0.040 in]
Operating Position (O.P.)	30,17 mm \pm 0,38 mm [1.188 in \pm 0.015 in]
Free Position (F.P.)	36,47 mm [1.436 in] max.
Material	Plastic
Housing Material	General Purpose Phenolic
High Temperature	204 °C [400 °F]
CE mark	61058-1
UL File #	E12252
CSA File #	LR41370
Agency Approvals and Standards	1054
Mounting Screw Size	3,53 mm [0.139 in]
Mounting Centers	25,4 mm [1 in]
Maximum Tightening Torque	0,33 N m [3.0 in lb]
Weight	34,5 g [0.076 lb]
Package Height	24,1 mm [0.95 in]
Package Width	17,5 mm [0.69 in]
Package Length	49,3 mm [1.94 in]
Recommended For	48,3 mm [1.9 in] (steel roller) lever applications
Availability	Global
UNSPSC Code	30211905
UNSPSC Commodity	30211905 Snap switches
Series Name	BZ Series

*Due to regional agency approval requirements, some products may not be available in your area.
Please contact your regional Honeywell office regarding your product of choice.*

