

Product Description

High degree of protection; Dynamic strain stability



Application range

- Equipment group II / Category 2G+1D
- Devices, machines and apparatus
- Mobile offshore and marine applications
- Chemical and petrochemical industry

Benefits

- High degree of protection
- Dynamic strain stability

Design

- metric connection thread acc. to EN 50262



Technical Data

Material

Body: Nickel plated brass O-Ring: NBR

Degree of protection

IP 68

Range of temperature

-30°C up to +90°C

Article List

Part number	Part designation / size	SW mm	Thread length D mm	Outer Ø mm	PU
SKINDICHT® BL-M ATEX					
52103103	12 x 1,5	16	5	17,8	50
52103113	16 x 1,5	20	5	22	50
52103123	20 x 1,5	24	6	26,4	50
52103133	25 x 1,5	29	7	31,9	50
52103143	32 x 1,5	36	8	39,6	25
52103153	40 x 1,5	45	8	49,5	25
52103163	50 x 1,5	54	9	59	10
52103173	63 x 1,5	67	10	73,5	10