

Metric

DURATOOL



DIN 338/BS 328

Flute Geometry

Standard Helix, right hand spiral

Surface finish

Blue

Point geometry

Up to 2.9mm - 118°

3.0mm and above - 135° split point

369266

Size	Flute length (mm)	Overall length (mm)	Order code
1.00	12	34	387-1034
1.20	16	38	155-2166
1.50	18	40	387-1046
1.60	20	43	155-2167
1.80	22	46	155-2337
2.00	24	53	387-1058
2.10	24	53	155-2169
2.20	27	53	155-2171
2.40	30	57	155-2575
2.50	30	57	387-1060
2.60	30	57	155-2172
2.70	33	61	155-2173
2.80	33	61	155-2174
3.00	33	61	387-1071
3.10	36	70	155-2175
3.20	36	70	155-2176
3.30	36	70	387-1290
3.40	39	70	155-5803
3.50	39	70	387-1083
3.60	39	70	155-2576
3.70	39	70	155-2339
3.80	43	75	155-2577
4.00	43	75	387-1095
4.10	43	75	155-2341
4.20	43	75	387-1307
4.30	47	80	155-2578
4.50	47	80	387-1101
4.80	52	86	155-2342
5.00	52	86	387-1113
5.10	52	86	155-2343
5.20	52	86	155-2344
5.50	57	93	387-1125
6.00	57	93	387-1137
6.20	63	101	155-5804
6.50	63	101	387-1149
6.80	69	109	387-1319
7.00	69	109	387-1150
7.50	69	109	387-1162
8.00	75	117	387-1174
8.50	75	117	387-1186
8.80	81	125	155-4317
9.00	81	125	387-1198
9.50	81	125	387-1204
10.00	87	133	387-1216
10.20	87	133	387-1435
10.50	87	133	387-1228
11.00	94	142	387-1230
11.50	94	142	387-1241
12.00	101	151	387-1253
12.50	101	151	387-1265
13.00	101	151	387-1277