

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0464369317

Status:


Active

Overview:

EXTreme Ten60 High-Power Connectors

Description:

EXTreme Ten60Power Right-Angle Receptacle with Side Guides, 2 DC Power Circuits, 30 Signal Circuits, Press Fit Tail



Series image - Reference only

Documents:	
3D Model	Packaging Specification 464361001-PK-000 (PDF)
Drawing (PDF)	Test Summary 464361000-TS-000 (PDF)
3D Model (PDF)	Datasheet (PDF)
Product Specification PS-46436-100-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E29179
General	
Product Family	PCB Receptacles
Series	46436
Application	Board-to-Board, Power, Signal
Comments	See Product Specification for details
Component Type	PCB Receptacle
Overview	EXTreme Ten60 High-Power Connectors
Product Name	EXTreme Ten60Power
Taxonomy	Board-to-Board Connectors
UPC	195842670846
Physical	
(p)ower-(s)ignal Configuration	2p - 30s
Circuits (Loaded)	32
Circuits (maximum)	32
Color - Resin	Black
Durability (mating cycles max)	200
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	Side, Yes
Keying to Mating Part	None
Lock to Mating Part	No
Mated Height	10.00mm
Material - Metal	High Conductivity Copper
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	14.081/g
Number of Rows	1, 5
Orientation	Right Angle
PC Tail Length	2.50mm, 3.28mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.58mm
Packaging Type	Tray
Pitch - Mating Interface	2.00mm, 5.50mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Stackable	No
Surface Mount Compatible (SMC)	No

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

46436 Series

Mates With

EXTreme Ten60Power Right-Angle Plug

464379317

Temperature Range - Operating
Termination Interface: Style

-40° to +105°C
Through Hole - Compliant Pin

Electrical
Current - Maximum per Contact
Grounding to PCB
Voltage - Maximum

60.0A
No
600V AC / 250V DC

Material Info

Reference - Drawing Numbers
Packaging Specification
Product Specification
Sales Drawing
Test Summary

464361001-PK-000
PS-46436-100-001
464369320-000
464361000-TS-000

This document was generated on 01/03/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION