

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0464363129](#)  
**Status:** **Active**  
**Overview:** [EXTreme Ten60 High-Power Connectors](#)  
**Description:** [EXTreme Ten60Power Right-Angle Receptacle with Side Guides, 20 Signal Circuits, Press Fit Tail](#)

**Documents:**

<a href="#">3D Model</a>	<a href="#">Packaging Specification PK-46436-001-000 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Test Summary 464361000-TS-000 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Product Specification PS-46436-100-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Packaging Specification 464361001-PK-000 (PDF)</a>	

**Agency Certification**


CSA	LR19980
UL	E29179

**General**

Product Family	PCB Receptacles
Series	<a href="#">46436</a>
Application	Board-to-Board, Signal
Comments	See Product Specification for details
Component Type	PCB Receptacle
Overview	<a href="#">EXTreme Ten60 High-Power Connectors</a>
Product Name	EXTreme Ten60Power
Signal Only	Yes
Taxonomy	Board-to-Board Connectors
UPC	193264606627

**Physical**

(p)ower-(s)ignal Configuration	0p - 20s
Circuits (Loaded)	20
Circuits (maximum)	20
Color - Resin	Black
Durability (mating cycles max)	200
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	Side, Yes
Keying to Mating Part	None
Lock to Mating Part	No
Mated Height	10.00mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	6.459/g
Number of Rows	5
Orientation	Right Angle
PC Tail Length	2.50mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.58mm
Packaging Type	Tray
Pitch - Mating Interface	2.00mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2022)4187-DC (10  
June 2022)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[46436 Series](#)

**Mates With**

[EXTreme Ten60Power Right-Angle Plug  
464373129](#)

Polarized to PCB	Yes
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole - Compliant Pin

**Electrical**

Current - Maximum per Contact	4.5A
Grounding to PCB	No
Voltage - Maximum	120V

**Material Info****Reference - Drawing Numbers**

Packaging Specification	464361001-PK-000, PK-46436-001-000
Product Specification	PS-46436-100-001
Sales Drawing	464363127-000
Test Summary	464361000-TS-000

This document was generated on 01/05/2023

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**