Rocker Switch

multicomp PRO



Wiring diagrams





Terminal type




RoHS Compliant

Diagram






z



Cut out



Termination



 Z
 Y
 X

 0.7-1.25
 30.2 +0.1
 22.0 +0.2 -0

 1.25-2.0
 30.6 +0.1
 22.0 +0.2 -0

 2.0-3.0
 30.8 +0.1
 22.0 +0.2 -0

Dimensions : Millimetres

Rating

20 (10) A / 250V AC 14 (14) A / 250V AC - 5E4 T120/55°C EN 61058

25 A / 125V AC 16 A /250V AC 3/4 HP - 125 / 250V AC T105°C UL 1054 CSA C22.2

Specification

Cutout	: 22mm × 30mm
Switch Action	: Latching
Illumination	: Illuminated
Shape	: Rectangular
Poles	: DPST
Switch Rating	: 20(10)A/250V AC
Terminals	: 6.3mm tabs
Colour	: Black body, Green illuminated switch
Switch Function	: On-Off
Voltage	: 250V
IP Rating	: IP65

Part Number Table

Description	Part Number
Rocker Switch, IP65, DPST, On-Off, Green	MP011250

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

