Rocker Switch

multicomp PRO



Wiring diagrams



RoHS Compliant

Terminal type



Rating

Cutout Switch Action

Shape

Poles

Illumination

Switch Rating

Switch Function : On-Off

Terminals

Colour

Voltage

IP Rating

Marking


Lamp


Specification

24V up to 20A T120/55°C

Specification

Diagram





Soffietto Bellow

10.2

Cut out



Z	Y	Х
0.7 1.25	22.0 0	30.2 ±0.1
1.25 2.0	22.0 +0.2	30.6 ±0.1
2.0 3.0	22.0 +0.2	30.8 ±0.1

Dimensions : Millimetres

Part Number Table

Description	Part Number	
Rocker Switch, IP65, DPST, On-Off, Green	MP011252	

: 22mm × 30mm

: Latching

: DPST

: 24V 20A

: 24V DC

: Black 01

: Incandescent

: IP65

: Illuminated

: Rectangular

: 6.3mm tabs

: Black body, Green illuminated switch

: Illumination "bright" version.

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

