

# Eaton CE15LN3A

Catalog Number: CE15LN3A

Eaton XT IEC contactor, No enclosure, 85A, 110-120 Vac, 50-60 Hz, 85A, Frame L, 140 mm, 50-60 Hz, 7.5 hp, Steel mounting plate, Three-pole, Non-reversing, No overload relay, Freedom, Contactor

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton XT IEC contactor	CE15LN3A
<b>UPC</b>	<b>Product Length/Depth</b>
782113604015	5.94 in
<b>Product Height</b>	<b>Product Width</b>
7.17 in	4.08 in
<b>Product Weight</b>	<b>Warranty</b>
8.05 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>Compliances</b>	<b>Certifications</b>
DIN VDE 0600 ISO 9000	UL Listed CSA Certified IEC Rated
<b>Catalog Notes</b>	
No enclosure	



## Product specifications

### Relay

No overload relay

### HP rating - max

7.5 hp

### Operation

Non-reversing

### Mounting method

Steel mounting plate

### Amperage Rating

85A

### Number Of Poles

Three-pole

### Frame size

140 mm

### Accessories

No enclosure

### Coil voltage

110-120 Vac, 50-60 Hz

### Series

Freedom

### Type

Contactor

### Continuous ampere rating

85 A

### Frequency rating

50-60 Hz

## Resources

### Catalogs

[Motor Starters and Contactors — Low Voltage Catalog](#)

[Eaton's Volume 5—Motor Control and Protection](#)

### Specifications and datasheets

[Eaton Specification Sheet - CE15LN3A](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)