

# Eaton C5000K2A

Catalog Number: C5000K2A

Eaton, type MTK, industrial control transformer, pv: 240 x 480v, 230 x 460v, 220 x 440v, taps: none, sv: 120/115/110v, 115°C, 5000 va, cu magnet wire

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Type MTK industrial control transformer	C5000K2A
	UPC
	786680125805
<b>Product Length/Depth</b>	<b>Product Height</b>
7.756 in	7.559 in
<b>Product Width</b>	<b>Product Weight</b>
9.016 in	89 lb
<b>Warranty</b>	<b>Compliances</b>
Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	<b>Certifications</b>
	CSA Certified cUL Certified UL Listed
	<b>Catalog Notes</b>
	Epoxy resin impregnated coil design, 50/60 Hz operation, 180°C insulation system



## Physical Attributes

Coil material  
Copper windings

Design  
MTK

Tap size  
None

## Performance Ratings

Primary voltage  
230 x 460 V  
240 x 480 V  
220 x 440 V

Temperature rating  
115°C

Volt ampere rating  
5000 VA

Secondary voltage  
120/115/110 V

## Resources

### Brochures

[Industrial control transformers brochure](#)  
[dry-type distribution transformer-flex center line card](#)

### Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)  
[Transformer distribution catalog, volume 2, tab 2](#)

### Specifications and datasheets

[Transformer consulting application guide](#)  
[Eaton Specification Sheet - C5000K2A](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)