## 200MHz ACTIVE DIFFERENTIAL PROBE TT-SX 200



	TT-SX 200
Order Number	15635
Bandwidth	DC to 200MHz
Attenuation	10:1
DC-Accuracy	±1%
Max. Input Voltage - Differential Mode (DC + peak AC)	±20V
Max. Input Voltage - Common Mode (DC + peak AC)	±60V
Maximum Input Voltage (each side to ground)	60V
Probe Load requirement	50Ohm
Power requirements	USB power adapter (included) USB cable (included)
Supplied Accessories	1 x 50 Ohm Feedthrough Termination, 1 x Hardcase 2 x Grabber (red & black), 2 x Pincer (red & black) 2 x Alligator Clips (red & black), 1 x Insulated BNC Cable, 100cm 1 x USB power lead, 1 x USB Power Adapter 220V EU Version 1 x factory calibration certificate

Technical data subject to change © Testec Elektronik GmbH 2022 info@testec.de www.testec.de

