

## Heater Series CS 060

**Art.-No. 06000.1-00**

(Standard version: 06000.0-00)

### Important data

#### 1. Mecha. Data<sup>1)</sup>

Housing: no difference

Connection/cable no difference

#### 2. Technical data<sup>1)</sup>

Operating voltage: 24V AC/DC (min 12V; max. 28V)<sup>2)</sup>

Inrush current max.: 10.0A

Operating temperature: -20 to +70°C (-4 to +158°F)

Pre-fuse: tbd

Air outlet temp.: tbd

Approval: VDE; GOST-TR



Photo: 06010.0-00

---

<sup>1)</sup> data that vary compared to the standard version

<sup>2)</sup> Operating with voltages below 15V AC/DC reduces heating performance by approx. 10%.

---

Specifications are subject to change without notice. Errors and omissions excepted. Suitability of this product for its intended use and any associated risks must be determined by the end customer/ buyer in its final application.