



Main

Range	TeSys
Range of Product	TeSys G
Device short name	LA9G
Product or Component Type	Plate
Product Compatibility	LC1G265...500 LC1G300...475
Device Application	Retrofit installation

Complementary

Height	9.45 in (240 mm)
Width	2.36 in (60 mm)
Depth	9.17 in (233 mm)
Net Weight	2.80 lb(US) (1.27 kg)
Quantity per Set	Set of 1

Environment

Ambient Air Temperature for Operation	-13...140 °F (-25...60 °C)
Ambient Air Temperature for Storage	-76...176 °F (-60...80 °C)
Operating altitude	9842.52 ft (3000 m) without derating 5000 m with derating factor
Pollution degree	3 IEC 60947-1

Ordering and shipping details

Category	22328-TESYS GIGA ACCESSORIES
Discount Schedule	I12
GTIN	00785901996866
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.36 in (6.0 cm)
Package 1 Width	9.25 in (23.5 cm)
Package 1 Length	9.45 in (24.0 cm)
Package 1 Weight	3.09 lb(US) (1.401 kg)
Unit Type of Package 2	S02
Number of Units in Package 2	3
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	10.21 lb(US) (4.63 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
PVC free	Yes
Halogen content performance	Halogen free plastic parts product