

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2025693005](#)
Status: **Active**
Overview: [Ultra-Fit Power Connectors](#)
Description: Ultra-Fit Plug Housing, 3.50mm Pitch, Single Row, 5 Circuits, Black, Glow-Wire Capable

Documents:

[Drawing \(PDF\)](#) [Datasheet \(PDF\)](#)
[Product Specification 2169461000-PS-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification 2025691000-PK-000 \(PDF\)](#)

General

Product Family [Crimp Housings](#)
Series [202569](#)
Application [Power, Wire-to-Wire](#)
Overview [Ultra-Fit Power Connectors](#)
Product Name [Ultra-Fit](#)
Taxonomy [Connector Housings](#)
UPC [195842150683](#)


Physical

Circuits (maximum) [5](#)
Color - Resin [Black](#)
Gender [Plug](#)
Glow-Wire Capable [Yes](#)
Keying to Mating Part [Yes](#)
Lock to Mating Part [Yes](#)
Material - Resin [Polyamide](#)
Net Weight [1.790/g](#)
Number of Rows [1](#)
Packaging Type [Bag](#)
Panel Mount [No](#)
Pitch - Mating Interface [3.50mm](#)
Pitch - Termination Interface [3.50mm](#)
Polarized to Mating Part [Yes](#)
Temperature Range - Operating [-40° to +105°C, -40° to +120°C](#)

Material Info

Reference - Drawing Numbers

Packaging Specification [2025691000-PK-000](#)
Product Specification [2169461000-PS-000](#)
Sales Drawing [2025691000-SD-000](#)



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[202569 Series](#)

Mates With

[Ultra-Fit Tangless Receptacle Housing 1722563105](#)

Use With

[Ultra-Fit Plug Terminal 216946](#) . [Ultra-Fit Tangless TPA 1722644005](#)