NEN!

## core

llghtlng

High-performance, lighting solutions at a highly competitive price

#### **CLK15 Key-ring Torch**

15 Lumens
10 Metre maximum range
5 Hours battery run-time
Supplied with key-fob attachment
4 x LR44 batteries (supplied)
1 Metre impact resistance
Supplied in 20pcs CDU Pack

Compact & handy, guarantees

light is always at hand!





#### **CL80 focusing Torch**

80 Lumens
Slide-Focus from Spot to Flood beam
50 Metre maximum range
2.5 Hours battery run-time
1 x AA battery (not supplied)
1.5 Metre impact resistance
Aerospace Aluminum casing

#### CL200 focusing Torch

200 Lumens
Slide-Focus from Spot to Flood beam
50 Metre maximum range
3 Hours battery run-time
3 x AAA batteries (not supplied)
1.5 Metre impact resistance
Aerospace Aluminum casing









NEN!

core

llghtlng

High-performance, lighting solutions at a highly competitive price



# NEW!

# core

lighting

High-performance, lighting solutions at a highly competitive price

### CLH200 rechargeable Head-Torch

200Lumens
55 Metre maximum range
5 Hours battery run-time
Inbuilt 'Li-on' rechargeable battery
USB/mini USB charger lead (supplied)
High, Medium, Low & SOS modes

Optional 'Motion Sensor' control enabling torch to be switched on/off by swiping hand in front of torch

Supplied in 12pcs CDU Pack

Incredible value for rechargeable
head-torch packed full of features!



#### CLH320 rechargeable focusing Torch

320Lumens
60 Metre maximum range
9 Hours battery run-time
Inbuilt 'Li-on' rechargeable battery
USB/mini USB charger lead (supplied)
High , Low & Flashing (white) modes
Solid & Flashing (red) modes
Illuminated 'Battery Life' indicator
Optional 'Motion Sensor' control
enabling torch to be switched on/off
by swiping hand in front of torch

Supplied in 12pcs CDU Pack

Full-spec high-powered rechargeable

option at highly competitive price!



NEN!

## core

lighting

High-performance, lighting solutions at a highly competitive price

#### CLW800 Wide area LED Work-lamp

#### 800Lumens

5 Hours battery run-time
High (100%) & Low (50%) modes
180 degree adjustable handle for
hanging-up or free standing
4 x AA Batteries (not supplied)

Supplied in 4 Colour hanging/ or free-standing display box
Incredible value for high-powered
Work-lamp easily capable of lighting-up large areas!



### CLW1150 rechargeable LED Work-lamp

#### 1150Lumens

5 Hours battery run-time
Inbuilt 'Li-on' rechargeable battery
High (100%) & Low (50%) modes
180 degree adjustable handle for
hanging-up or free standing
Includes 'Battery Life ' indicator display
'Power Out' port enables option to
recharge other powered products
such as smart phones/tablets

Supplied in 4 Colour hanging/ or freestanding display box Incredible value for high-powered Rechargeable Work-lamp easily capable of lighting-up large areas!

