

**Series: Stick Antenna** 

#### **TECHNICAL DATA SHEET**

**Description**: 698-960/1710-3800MHz Stick

Antenna with RA SMA connector

PART NUMBER: W1096X

### Features:

- 4G/5G Stick Antenna
- Performance across the LTE frequency bands
- 698-960/1710-2690/3400-3800 MHz
- Up to 2 dBi Gain
- Right Angle SMA or RP SMA Male connector
- IP65

### **Applications:**

- 4G / 5G Radios
- · Router, Hub or Access point
- Small Base Station
- Femto Cell
- SOHO

All dimensions are in mm / inches

Issue: 2033

In the effort to improve our products, we reserve the right to make changes judged to be necessary. CONFIDENTIAL AND PROPRIETARY INFORMATION

This document contains confidential and proprietary information of Pulse Electronics, Inc. (Pulse) and is protected by copyright, trade secret and other state and federal laws. Its receipt or possession does not convey any rights to reproduce, disclose its contents, or to manufacture, use or sell anything it may describe. Reproduction, disclosure or use without specific written authorization of Pulse is strictly forbidden. For more information:





**Description**: 698-960/1710-3800MHz Stick

Antenna with RA SMA connector

PART NUMBER: W1096X

**Series: Stick Antenna** 

### This document covers all product variants of the following product family

Antennas	Connector
W1096	RA RP SMA Male
W1096RM	RA SMA Male



Series: Stick Antenna

#### **TECHNICAL DATA SHEET**

**Description**: 698-960/1710-3800MHz Stick

Antenna with RA SMA connector

PART NUMBER: W1096X

### **ELECTRICAL SPECIFICATIONS**

Antenna Type Monopole antenna

Frequency 698-960/1710-2690/3400-3800 MHz

Nominal Impedance 50  $\Omega$ 

VSWR(Max) 3.5:1 / 2:1 / 4:1

Radiation Pattern Omni

Gain 698-960MHz >-3 dBi
Gain 1710-2690MHz >1.5 dBi

Gain 3400-3800MHz >-0.5 dBi

Efficiency 698-960MHz >30 %

Efficiency 1710-2690MHz >60 %

Efficiency 3400-3800MHz >45 %

Polarization Linear

Power Withstanding 3 W

### **MECHANICAL SPECIFICATIONS**

Overall Length 112±3mm

Weight 13g

Antenna Color / Material Black

Connector type W1096: Right Angle RP SMA Male, Silver Ni plating

W1096RM: Right Angle SMA Male, Silver Ni plating

#### **ENVIRONMENTAL SPECIFICATIONS**

Operating Temperature -40 °C to +80 °C

Storage Temperature -40 °C to +80 °C

Ingress Protection IP65

RoHS Compliant Yes

Issue: 2033






**Description**: 698-960/1710-3800MHz Stick

Antenna with RA SMA connector

PART NUMBER: W1096X

## **Series: Stick Antenna**

### **MECHANICAL DRAWING**



Issue: 2033





**Description**: 698-960/1710-3800MHz Stick


Antenna with RA SMA connector

PART NUMBER: W1096X

### **Series: Stick Antenna**

### **TEST SETUP**

## ground plane





**Description**: 698-960/1710-3800MHz Stick


Antenna with RA SMA connector

PART NUMBER: W1096X

# Series: Stick Antenna

### **TEST SETUP**

### **VSWR**:







**Description**: 698-960/1710-3800MHz Stick


Antenna with RA SMA connector

PART NUMBER: W1096X

## **Series: Stick Antenna**

### **Total radiated Efficiency**

## Efficiency curve:









**Description**: 698-960/1710-3800MHz Stick


Antenna with RA SMA connector

PART NUMBER: W1096X

## **Series: Stick Antenna**

### **Maximum peak Gain**

## Peak gain curve:







**Description**: 698-960/1710-3800MHz Stick


Antenna with RA SMA connector


PART NUMBER: W1096X


### **Series: Stick Antenna**

### **CHARTS**

## Curves at 698, 829 and 960MHz:









**Description**: 698-960/1710-3800MHz Stick


Antenna with RA SMA connector


PART NUMBER: W1096X


### **Series: Stick Antenna**

#### **CHARTS**

## Curves at 1710, 2200 and 2690MHz:







Issue: 2033



**Description**: 698-960/1710-3800MHz Stick


Antenna with RA SMA connector


PART NUMBER: W1096X


### **Series: Stick Antenna**

### **CHARTS**

## Curves at 3400,3600 and 3800MHz:









**Series: Stick Antenna** 

#### **TECHNICAL DATA SHEET**

**Description**: 698-960/1710-3800MHz Stick

Antenna with RA SMA connector

PART NUMBER: W1096X

### **PACKAGING**



20pcs ants each small bag

Item	QTY
Each small bag	20pcs
Each big bag	400pcs(20pcs small bags)
Each box	2000pcs