

TECHNICAL DATA

Fluke TPS FLEX 18 Flexible Current Probe



Specifications: Fluke TPS FLEX 18 Flexible Current Probe

General Specifications	
Measuring Range selectable per software	1 A to 100 A
	5 A to 500 A
Peak current for sinusoidal currents	240 A
	1350 A
Intrinsic error	1%
Frequency Range	45 Hz to 3.0 kHz
Operating Voltage	300 V CAT IV
Phase Error	0.5°
Jaw Opening	45 cm length
	2 m cable
Errors in % of measuring range at 23°C ± 2 K; 74°F ± 2 K, for 48 to 65 Hz Phase angle error at nominal current Imax maximum current without time limit (for AC and DC shunts)	

Ordering information



Fluke TPS FLEX 18

Flexible Current Probe

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2023 Fluke Corporation.
Specifications subject to change without notice.
02/2023

**Modification of this document is not permitted
without written permission from Fluke Corporation.**