

MPP-PFT-ix-F-P



Part number	09 51 521 0001
Specification	MPP-PFT-ix-F-P
HARTING eCatalogue	https://b2b.harting.com/09515210001

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Connectors
Series	HARTING Mini PushPull
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	Without board locks

Version

Locking type	PushPull

Technical characteristics

Limiting temperature	-40 +70 °C
Storage temperature	-60 +85 °C
Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP65 / IP67

Material properties

Material (hood/housing)	Polybutylene terephthalate (PBT)
Colour (hood/housing)	Black
Material (seal)	PTS
Colour (seal)	Yellow
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	е



Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Commercial data

Packaging size	1
Country of origin	Germany
European customs tariff number	39269097
GTIN	5713140224100
eCl@ss	27440202 Shell for industrial connectors