


MPP-PFT-ix/ix-10p-F-P-B-cod



Part number	09 51 221 0002
Specification	MPP-PFT-ix/ix-10p-F-P-B-cod
HARTING eCatalogue	https://b2b.harting.com/09512210002

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Connectors
Series	HARTING Mini PushPull
Identification	ix Industrial [®]
Element	Panel feed trough set
Type of hood/housing	Bulkhead mounted housing

Version

Shielding	Fully shielded, 360° shielding contact
Number of contacts	10
Coding	Type B
Locking type	PushPull
Pack contents	incl. seal, 2x HARTING ix Industrial $^{\!8}$ -jack type B (Signal) and board drillings for M2.5

Technical characteristics

Rated current	1.5 A
Rated voltage	50 V AC 60 V DC
Contact resistance	≤30 mΩ
Shielding resistance	≤100 mΩ
Limiting temperature	-40 +70 °C
Storage temperature	-60 +85 °C
Insertion force	≤25 N
Withdrawal force	≤25 N

Page 1 / 2 | Creation date 2023-01-20 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application.

HARTING Stiftung & Co. KG | Marienwerderstr. 3 | 32339 Espelkamp | Germany



Technical characteristics

Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP65 / IP67
Test voltage U _{r.m.s.}	0.5 kV (contact-contact)
	0.5 kV (contact-shielding)

Material properties

Material (insert)	Liquid crystal polymer (LCP)
Colour (insert)	Black
Material (contacts)	Copper alloy
Material (hood/housing)	Polybutylene terephthalate (PBT)
Colour (hood/housing)	Black
Material (seal)	PTS
Colour (seal)	Yellow
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Specifications and approvals

Specifications	IEC 61076-3-124 Type B

Commercial data

Packaging size	1
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140223431
eCl@ss	27440114 Rectangular connector (for field assembly)