

MPP-CC-IDC-ix-10p-M-P-STR A-cod AWG28-26



Part number	09 51 121 0001
Specification	MPP-CC-IDC-ix-10p-M-P-STR A-cod AWG28-26
HARTING eCatalogue	https://b2b.harting.com/09511210001

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Connectors
Series	HARTING Mini PushPull
Identification	ix Industrial [®]
Element	Connector sets

Version

Termination method	IDC termination
Shielding	Fully shielded, 360° shielding contact
Number of contacts	8
further contacts	+ 2x GND
Coding	Type A
Locking type	PushPull
Pack contents	incl. housing, HARTING ix Industrial [®] -connector type A, shielding and cable gland

Technical characteristics

Conductor cross-section	0.09 0.14 mm²
Conductor cross-section	AWG 28 AWG 26
Wire outer diameter	≤1.15 mm
Rated current	1.5 A
Rated voltage	50 V AC 60 V DC
Transmission characteristics	Cat. 6 _A Class E _A up to 500 MHz



Technical characteristics

Data rate	10 Mbit/s 100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
	10 Gbit/s
Contact resistance	≤30 mΩ
Shielding resistance	≤100 mΩ
Limiting temperature	-40 +70 °C
Storage temperature	-60 +85 °C
Insertion force	≤25 N
Withdrawal force	≤25 N
Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP65 / IP67
Cable diameter	4.5 7.5 mm
Test voltage U _{r.m.s.}	0.5 kV

Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	Black
Material (contacts)	Copper alloy
Material (hood/housing)	Polybutylene terephthalate (PBT) / PA66
Colour (hood/housing)	Black
Material (seal)	HNBR / NBR
Colour (seal)	Black
Material (locking)	Polybutylene terephthalate (PBT)
Colour (locking)	Yellow
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol



Material properties

ECHA SCIP number 5b0b428a-c671-4c90-9b6d-16804ea5737a

California Proposition 65 substances Not contained

Specifications and approvals

Specifications	IEC 61076-3-124 Type A
Specifications	EN 50173-1

Commercial data

Packaging size	1
Net weight	26 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140223387
eCl@ss	27440114 Rectangular connector (for field assembly)