

MPP-CC-IDC-ix-10p-M-P-STR B-cod AWG28-26



Image is for illustration purposes only. Please refer to product description.

Part number	09 51 121 0002
Specification	MPP-CC-IDC-ix-10p-M-P-STR B-cod AWG28-26
HARTING eCatalogue	https://b2b.harting.com/09511210002

Identification

Category	Connectors
Series	HARTING Mini PushPull
Identification	ix Industrial®
Element	Connector sets

Version

Termination method	IDC termination
Shielding	Fully shielded, 360° shielding contact
Number of contacts	10
Coding	Type B
Locking type	PushPull
Pack contents	incl. housing, HARTING ix Industrial®-connector type B, shielding and cable gland

Technical characteristics

Conductor cross-section	0.09 ... 0.14 mm ²
Conductor cross-section	AWG 28 ... AWG 26
Wire outer diameter	≤1.15 mm
Rated current	1.5 A
Rated voltage	50 V AC 60 V DC
Contact resistance	≤30 mΩ
Shielding resistance	≤100 mΩ
Limiting temperature	-40 ... +70 °C



Pushing Performance
Since 1945

Technical characteristics

Storage temperature	-60 ... +85 °C
Insertion force	≤25 N
Withdrawal force	≤25 N
Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP65 / IP67
Cable diameter	4.5 ... 7.5 mm
Test voltage $U_{r.m.s.}$	0.5 kV

Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	Black
Material (contacts)	Copper alloy
Material (hood/housing)	Polybutylene terephthalate (PBT) / PA66
Colour (hood/housing)	Black
Material (seal)	HNBR / NBR
Colour (seal)	Black
Material (locking)	Polybutylene terephthalate (PBT)
Colour (locking)	Yellow
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol

Specifications and approvals

Specifications	IEC 61076-3-124 Type B
----------------	------------------------

Commercial data

Packaging size	1
Net weight	9.86 g
Country of origin	Germany



Pushing Performance
Since 1945

Commercial data

European customs tariff number	85366990
GTIN	5713140223394
eCl@ss	27440114 Rectangular connector (for field assembly)
