

MPP ix Tp A 4x2xAWG26 Cat6A PVC out 0,5m



Image is for illustration purposes only. Please refer to product description.

Part number	33 48 343 4806 005
Specification	MPP ix Tp A 4x2xAWG26 Cat6A PVC out 0,5m
HARTING eCatalogue	https://b2b.harting.com/33483434806005

Identification

Category	System cabling
Series	HARTING Mini PushPull
Identification	ix Industrial®
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	HARTING Mini PushPull ix Industrial® Type A Overmoulded
Connector 2	HARTING Mini PushPull ix Industrial® Type A Overmoulded
Type of cable	Copper cable (round)
Description of the cable	UV resistant

Version

Cable length	0.5 m
Number of cores	8
Core structure	4x 2x AWG 26/7
Termination method	IDC termination

Technical characteristics

Transmission characteristics	Cat. 6A Class EA up to 500 MHz
------------------------------	--------------------------------



Pushing Performance
Since 1945

Technical characteristics

Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
	10 Gbit/s
Limiting temperature	-20 ... +80 °C unmoved
	-20 ... +80 °C moved

Material properties

Material (cable)	PVC
Colour (cable)	Black
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 61076-3-124
----------------	-----------------

Commercial data

Packaging size	1
Country of origin	Latvia
European customs tariff number	85444290
GTIN	5713140282865
eCl@ss	27060390 Ready-made data cable (unspecified)