

MPP ix Tp A 4x2xAWG26 Cat6A PVC out 7,5m



Part number	33 48 343 4806 075
Specification	MPP ix Tp A 4x2xAWG26 Cat6A PVC out 7,5m
HARTING eCatalogue	https://b2b.harting.com/33483434806075

Image is for illustration purposes only. Please refer to product description.

Identification

Category	System cabling
Series	HARTING Mini PushPull
Identification	ix Industrial [®]
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	HARTING Mini PushPull ix Industrial [®] Type A Overmoulded
Connector 2	HARTING Mini PushPull ix Industrial [®] Type A Overmoulded
Type of cable	Copper cable (round)
Description of the cable	UV resistant

Version

Cable length	7.5 m
Number of cores	8
Core structure	4x 2x AWG 26/7
Termination method	IDC termination

Technical characteristics

Transmission characteristics	Cat. 6 _A Class E _A up to 500 MHz	



Technical characteristics

Data rate	10 Mbit/s 100 Mbit/s 1 Gbit/s 2.5 Gbit/s 5 Gbit/s 10 Gbit/s
Limiting temperature	-20 +80 °C unmoved -20 +80 °C moved

Material properties

Material (cable)	PVC
Colour (cable)	Black
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 61076-3-124	
Specifications	IEC 01070-3-124	

Commercial data

Packaging size	1
Country of origin	Latvia
European customs tariff number	85444290
GTIN	5713140282940
eCl@ss	27060390 Ready-made data cable (unspecified)