


C5A11UXXX

(M12 Cordset, 5 Position, 22 AWG Unshielded, Male Straight to Free End)





- Mueller's C5A10UXXX is an M12 5-pin single ended, unshielded instrumentation cable with a straight male connector on one end and free at the other.
- Keyway A Coding
- Utilizes a 5-conductor 22 AWG PVC-insulated, unshielded cable.
- Ratings:

o Current: 4 A

Voltage: 250 V AC/DC

Material:

Coupling Nuts – Nickel Plated Brass

Pins/Contacts – Gold Plated Brass

• Length: The "U" in the model number represents unit of measurement.

Either: Meters (M), Feet (F)

• Length: The "XXX" in the model number represents length. Standard lengths are 2, 5, and 10 meters. Any other lengths available upon request.

Meets Standard: IEC 61076-2-101

Protection Class: IEC IP68

Toll Free: 800.955.2629

Phone: 330.780.2525

Fax: 330.780.2524

RoHS 3 Co	mpliant		
Mueller Electric Cor 2850 Gilchrist Rd. B Akron, OH 44305	npany ld 5A wwv	v.muellerelectric.com	Toll Free: 800.955.2629 Phone: 330.780.2525 Fax: 330.780.2524