


C4C02UXXX

(M12 Cordset, 4 Position, 18 AWG, Female Straight to Free End)





- Mueller's C4C02UXXX is an M12 4-pin single ended instrumentation cable with a straight female connector on one end and free at the other.
- Keyway A Coding
- Utilizes our 4-conductor 18 AWG TPE-insulated cable.
- Ratings:
 - o Current: 4 A
 - Voltage: 250 V AC/DC
 - O Temperature Range: -40° C to 105° C
- Material:
 - o Coupling Nuts Aluminum
 - Pins/Contacts Gold Plated Brass
- Length: The "U" in the model number represents unit of measurement.
 Either: Meters (M), Feet (F)
- Length: The "XXX" in the model number represents length. Standard lengths are 2, 5, and 10 meters. Any other lengths available upon request.
- Meets Standard: IEC 61076-2-101
- Protection Class: IEC IP68
- RoHS 3 Compliant

Toll Free: 800.955.2629

Phone: 330.780.2525

Fax: 330.780.2524