

C3AD04UXXX

(M12 Cordset, 3 Position, 22 AWG Shielded, Male Straight to Female Right Angle)



- Mueller's C3AD04UXXX is an M12 3-pin double ended, shielded instrumentation cable with a straight male connector on one end and a right angle female at the other.
- Keyway A Coding
- Utilizes a 3-conductor 22 AWG PVC-insulated, shielded cable.
- Ratings:
 - o Current: 4 A
 - o Voltage: 250 V AC/DC
- Material:
 - Coupling Nuts Nickel Plated Brass
 - Pins/Contacts Gold Plated Brass
- Length: The "U" in the model number represents unit of measurement. Either: Meters (M), Feet (F)
- Length: The "XXX" in the model number represents length. Standard lengths are 2, 5, and 10 meters. Any other lengths available upon request.
- Meets Standard: IEC 61076-2-101
- Protection Class: IEC IP68
- RoHS 3 Compliant

Toll Free: 800.955.2629

Phone: 330.780.2525

Fax: 330.780.2524