


C4D10UXXX

(M12 Cordset, 4 Position, 22 AWG Unshielded, Female Right Angle to Free End)





Pin Out		
End 1	Color	End 2
1	Brown	
2	White	Free End
3	Blue	Free Ena
4	Black	

Toll Free: 800.955.2629

Phone: 330.780.2525

Fax: 330.780.2524

- Mueller's C4D10UXXX is an M12 4-pin single ended, unshielded instrumentation cable with a right-angle female connector on one end and free at the other.
- Keyway A Coding
- Utilizes a 4-conductor 22 AWG PVC-insulated, unshielded cable.
- Ratings:
 - o Current: 4 A
 - o Voltage: 250 V AC/DC
- Material:
 - Coupling Nuts Nickel Plated Brass
 - o Pins/Contacts Gold Plated Brass
- Length: The "U" in the model number represents unit of measurement.

Either: Meters (M), Feet (F)

- Length: The "XXX" in the model number represents length. Standard lengths are 2, 5, and 10 meters. Any other lengths available upon request.
- Meets Standard: IEC 61076-2-101
- Protection Class: IEC IP68
- RoHS 3 Compliant