


C5D11UXXX

(M12 Cordset, 5 Position, 22 AWG Unshielded, Female Right Angle to Free End)





| Pin Out | | |
|---------|-------|----------|
| End 1 | Color | End 2 |
| 1 | Brown | |
| 2 | White | |
| 3 | Blue | Free End |
| 4 | Black | |
| 5 | Grey | |

Toll Free: 800.955.2629

Phone: 330.780.2525

Fax: 330.780.2524

- Mueller's C5D11UXXX is an M12 5-pin single ended, unshielded instrumentation cable with a right-angle female connector on one end and free at the other.
- Keyway A Coding
- Utilizes a 5-conductor 22 AWG PVC-insulated. unshielded cable.
- Ratings:
 - o Current: 4 A
 - o Voltage: 250 V AC/DC
- Material:
 - Coupling Nuts Nickel Plated Brass
 - Pins/Contacts Gold Plated Brass
- Length: The "U" in the model number represents unit of measurement. Either: Meters (M), Feet (F)
- Length: The "XXX" in the model number represents length. Standard lengths are 2, 5, and 10 meters. Any other lengths available upon request.
- Meets Standard: IEC 61076-2-101
- Protection Class: IEC IP68
- RoHS 3 Compliant