




AI-T00203

(Receptacle, M12 Rear Mount, 4-Position Female Straight-Open, PG9 Threads, 22 AWG, 2M)









| Pin Out | | |
|---------|-------|------|
| J1 | COLOR | J2 |
| 1 | BROWN | |
| 2 | WHITE | |
| 3 | BLUE | OPEN |
| 4 | BLACK | |

Toll Free: 800.955.2629

Phone: 330.780.2525

Fax: 330.780.2524

- Mueller's Al-T00203 is a cable assembly that has a 4-position rear mount M12 female receptacle to open end, 22 AWG, 2 meters.
- Shell size for connector: M12 (A Coding)
- Cable Material: UL 1569 22AWG Hook Up Wire
 - Overall length = 6.56' (2M)
- Shell: 18x18mm PG9 threaded rear mount
 - Material: Nickel Plated Brass
- Rating:

o Voltage: 250V AC/DC

o Current: 4 Amps

o Ambient Temperature: -40°C to 85°C

• Standard: IEC 61076-2-101

• Waterproof: IP67/IP68

• RoHS 3 Compliant