

AI-T00214

(Receptacle, M12 Front Mount, 5-Position Female Straight-Open, PG9 Threads, 22 AWG, 2M)



- Mueller's AI-T00214 is a cable assembly that has a 5-position front mount M12 female receptacle to open end, 22 AWG, 2 meters.
- Shell size for connector: M12 (A Coding)
- Cable Material: UL 1569 22AWG Hook Up Wire
 - Overall length = 6.56' (2M)
- Shell: 18x18mm PG9 threaded front mount
 - o Material: Nickel Plated Brass
- Rating:
 - Voltage: 60V AC/DC
 - Current: 4 Amps
 - Ambient Temperature: -40°C to 85°C
 - Standard: IEC 61076-2-101
- Waterproof: IP67/IP68
- RoHS 3 Compliant

Mueller Electric Company 2850 Gilchrist Rd. Bld 5A Akron, OH 44305

www.muellerelectric.com

Toll Free: 800.955.2629 Phone: 330.780.2525 Fax: 330.780.2524