



## AI-T00208


(Receptacle, M12 Rear Mount, 5-Position Female Straight-Open, ¼-18NPT Threads, 22 AWG, 2M)







J1



	i iii Out	
J1	COLOR	J2
1	BROWN	
2	WHITE	OPEN
3	BLUE	OPEN
4	BLACK	
5	GRAY	

Toll Free: 800.955.2629

Phone: 330.780.2525

Fax: 330.780.2524

Pin Out

- Mueller's AI-T00208 is a cable assembly that has a 5-position rear mount M12 female receptacle to open end, 22 AWG, 2 meters.
- Shell size for connector: M12 (A Coding)
- Cable Material: UL 1569 22AWG Hook Up Wire
  - Overall length = 6.56' (2M)
- Shell: 18x18mm ¼-18NPT threaded rear mount
  - Material: Nickel Plated Brass
- Rating:

Voltage: 60V AC/DCCurrent: 4 Amps

Ambient Temperature: -40°C to 85°C
Standard: IEC 61076-2-101

• Waterproof: IP67/IP68

• RoHS 3 Compliant