


AI-T00210


(Receptacle, M12 Rear Mount, 12-Position Male Straight-Open, PG9 Threads, 24 AWG, 0.5M)




Pin Out









•	Mueller's AI-T00210 is a cable assembly that has a 12-position rear mount
	M12 Male receptacle to open end, 24 AWG, 0.5 meters.

• Shell size for connector: M12 (A Coding)

• Cable Material: 24AWG Hook Up Wire

Overall length = 1.64' (0.5M)

• Shell: 18x20.8mm PG9 threaded rear mount

Material: Nickel Plated Brass

• Rating:

Voltage: 30V AC/DC
Current: 1.5 Amps
Ambient Temperature: -40°C to 85°C

• Standard: IEC 61076-2-101

• Waterproof: IP67/IP68

• RoHS 3 Compliant

Mueller Electric Company 2850 Gilchrist Rd. Bld 5A Akron, OH 44305

www.muellerelectric.com

Toll Free: 800.955.2629 Phone: 330.780.2525 Fax: 330.780.2524