



AI-T00213

(Receptacle, M12 Rear Mount, 4-Position Male Straight-Open, PG9 Threads, 22 AWG, 1M)







1 2

J1 COLOR J2 1 BROWN 2 WHITE
2 WHITE
2 WHITE
OPEN
3 BLUE
4 BLACK

- Mueller's Al-T00213 is a cable assembly that has a 4-position rear mount M12 Male receptacle to open end, 22 AWG, 1 meter.
- Shell size for connector: M12 (A Coding)
- Cable Material: UL 1569 22AWG Hook Up Wire
 - Overall length = 3.28' (1M)
- Shell: 18x25.3mm PG9 threaded rear mount
 - Material: Nickel Plated Brass
- Rating:

Voltage: 250V AC/DC

o Current: 4 Amps

Ambient Temperature: -40°C to 85°C

Standard: IEC 61076-2-101Waterproof: IP67/IP68

RoHS 3 Compliant

Mueller Electric Company 2850 Gilchrist Rd. Bld 5A Akron, OH 44305

www.muellerelectric.com

Toll Free: 800.955.2629 Phone: 330.780.2525 Fax: 330.780.2524