


AI-T00215

(Receptacle, M12 Front Mount, 12-Position Male Straight-Open, PG9 Threads, 24 AWG, 0.5M)



- Mueller's AI-T00215 is a cable assembly that has a 12-position front mount M12 Male receptacle to open end, 24 AWG, 0.5 meters.
- Shell size for connector: M12 (A Coding)
- Cable Material: 24AWG Hook Up Wire
 - \circ Overall length = 1.64' (0.5M)
- Shell: 18.0x21.5 mm PG9 threaded front mount
 - Material: Nickel Plated Brass
- Rating:
 - Voltage: 30V AC/DC
 - Current: 1.5 Amps
 - Ambient Temperature: -40°C to 85°C
 - Standard: IEC 61076-2-101
- Waterproof:
- RoHS 3 Compliant

Mueller Electric Company 2850 Gilchrist Rd. Bld 5A Akron, OH 44305

www.muellerelectric.com

IP67/IP68

Toll Free: 800.955.2629 Phone: 330.780.2525 Fax: 330.780.2524