

Home

EKI-2706G-1GFPI-BU

5GE+1G SFP Unmanaged Ind. PoE Switch W/T



- Supports 10/100/1000 Mbps Auto Negotiation (EKI-2706G)
- Supports jumbo frame transmission up to 9 kbytes
- DIN-rail with IP30 metal mechanism
- Redundant 24~48 VDC power input(BE Version)
- Provides broadcast storm protection
- 4 x IEEE 802.3 af/at PoE ports + 1 x Gigabit Copper + 1 Gigabit SFP ports

Resouces
[Extended Specifications](#) |

Contact Advantech



Specifications

Customer Service

- Warranty Policy
- Online Catalog
- Download Center
- Terms and Conditions

Contact us

- Privacy
- Site Map
- Contact us

G

Sh



Category

Attribute

Value

Power

Power Connector Type

6-pin removable screw terminal (power & relay)

Power

Power Consumption

Max 2W

Power

Power Input (DC)

24 ~ 48 VDC

Interface

Port Number

6

Environment

Relative Humidity

10~95%

Environment

Temperature (Operating Range)

-40 ~ 75°C (-40 ~ 167°F)

Environment

Temperature (Storage Range)

-40 ~ 85°C (-40 ~ 185°F)

Mechanism

Dimensions (W x H x D)

30 x 140 x 95 mm (1.18' x 5.51' x 3.74 in.)

Mechanism

Enclosure (Metal)

Metal

Mechanism

IP Rating

IP30

Mechanism

Customer Service

[Warranty Policy](#)

[Online Catalog](#)

[Download Center](#)

[Terms and Conditions](#)

Contact us

[Privacy](#)

[Site Map](#)

[Contact us](#)



Category

Attribute

Value

Power

Power Connector Type

6-pin removable screw terminal (power & relay)

Power

Power Consumption

Max 2W

Power

Power Input (DC)

24 ~ 48 VDC

Interface

Port Number

6

Environment

Relative Humidity

10~95%

Environment

Temperature (Operating Range)

-40 ~ 75°C (-40 ~ 167°F)

Environment

Temperature (Storage Range)

-40 ~ 85°C (-40 ~ 185°F)

Mechanism

Dimensions (W x H x D)

30 x 140 x 95 mm (1.18' x 5.51' x 3.74 in.)

Mechanism

Enclosure (Metal)

Metal

Mechanism

IP Rating

IP30

Mechanism