



the rules of sound



PL60

Ceiling speaker

The PL60 is a ceiling speaker with an elegant design, intended for recess installation in false ceilings or panels. It is ideal for the reproduction of announcements and background music and features a multiplesocket line transformer for use with constant voltage systems.

- Plastic body and white metal grid RAL 9003.
- Highly-efficient dual-cone extended range speaker, diameter 160 mm (6").
- Easy to install thanks to a special tripleholdfast system, without the need for screws and other retention parts.
- Transformer for constant voltage 70V-100V lines with pre-selection on four power levels.
- Accessory A 1360 available for ceiling installation.

SPECIFICATIONS	Description	Specifications
Type		Ceiling speaker
Installation system		Flush-mounted A1360
Nominal/maximum power		6/10 W
Constant voltage		[100 V]: 6-3-1,5 W - [70 V]: 6-3-1,5-0,75 W
Impedance		4 Ω
Frequency response		80÷14 kHz
Sensitivity		91 dB (1W/1m)
Maximum sound pressure		99/102 dB
Angle of coverage		[1.000 Hz]: 70° - [2.000 Hz]: 80°
Dimensions		Ø 204x75 mm.
Maximum protrusion		6 mm.
Flush-mounting hole		Ø 180 mm.
Weight		0,8 Kg.
Accessories included		-
Optional accessories		A 1360 White base for surface mounting
Speaker		6"
Protection level		-
Connectors		Screw terminals