

## GROUNDING & BONDING BRAID, 11.84 KCMIL, 7.87"

### CATALOG NUMBER

**BJ6-200S**



### CERTIFICATIONS



### FEATURES

Ready to use out of the box, saving installation time and labor

Allows for bending very close to the contact area

RoHS compliant

### PRODUCT ATTRIBUTES

Article Number: 556910

Finish: Tinned

Material: Copper

Working Temperature: 221 °F Max

Ampacity: 45 A

Cross Section: 11.840 kcmil

Length: 7.870"


Wire Diameter: 0.006"

Hole Size: 0.260"

Unit Weight: 0.030 lb

## DIAGRAMS

---



## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**