

CATALOG NUMBER

UTB30DP



CERTIFICATIONS



FEATURES

Compact design universal transient barrier provides protection of low-voltage circuits and transducers

Separate plug and base design allows hot swappable module replacement

Multi-stage protection and fine over-voltage protection helps ensure lowest residual surge voltages reach sensitive equipment

Common-mode and differential-mode protection protects against both possible surge conditions

Surge rating to 20 kA 8/20 μ s is ideal for exposed wiring

Allows for protection of 25 analog signals or 50 digital signals per linear foot (0,3 m) of DIN rail space

PRODUCT ATTRIBUTES

Nominal System Voltage (U_n): 10 - 21 VAC;15 - 30 VDC

Max Continuous Operating Voltage (U_c): 23 VAC;33 VDC

Rated Load Current (I_L): 800 mA

Frequency: 2 MHz

Loop Resistance: 0.6 Ω

Max Discharge Current (I_{max}), L+L-PE: 20 kA 8/20 μ s

Protection Modes: Common;Differential

Technology: Gas Discharge Tube (GDT);Metal Oxide Varistor (MOV);Silicon Avalanche Diode (SAD)

Voltage Protection Level (Up), L-L: 44 V @ 3 kA

Connection, Stranded: #18 – #12

Mounting: 35 mm top hat DIN rail

Temperature: -4 to 149 °F

Enclosure Material: UL® 94V-0 Thermoplastic

Enclosure Rating: IP 20;NEMA®-1

Depth (D): 3.350"

Height (H): 3.540"

Width (W): 0.470"


Unit Weight: 0.200 lb

Certification Details: UL® 497B

Complies With: ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C

Replacement Module: UTB30DPM

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER