



Polyester self-closing sleeving

Helagaine Twist-In

Helagaine Twist-In is used to bundle and protect pre-terminated cables in machine-building and automation, electrical installations and automobile and truck manufacturing.

Helagaine Twist-In is also available in practical 2 m and 5 m lengths for use in the home or office.

Features and benefits

- Self-closing sleeve made of polyester
- Very good protection against abrasion
- Ideal for retro-fitting
- Quick and easy installation and removal
- Allows to bundle for inspection, maintenance and assembly
- Small range of sizes covers a wide range of applications



Helagaine Twist-In enables easy access to cables and wires for assembly, inspection and maintenance.



www.HellermannTyton.co.uk/Twist-In-cat22

MATERIAL	Polyester (PET)
Operating Temperature	-50 °C to +125 °C
Melting Point	+255 °C
Flammability	self-extinguishing, FMVSS 302



TYPE	Bundle Ø min.	Bundle Ø max.	Colour	Reel Length	Tools	Article-No.
Twist-In 05	4	5	Black (BK)	150 m	45	170-01000
Twist-In 08	5	8	Black (BK)	100 m	45	170-01001
Twist-In 13	10	13	Black (BK)	50 m	45	170-01002
Twist-In 19	16	19	Black (BK)	25 m	45	170-01004
Twist-In 25	19	25	Black (BK)	25 m	45	170-01005
Twist-In 29	25	29	Black (BK)	15 m	45	170-01006
Twist-In 32	29	32	Black (BK)	15 m	45	170-01007
Twist-In 38	32	38	Black (BK)	15 m	45	170-01008
Twist-In 50	38	50	Black (BK)	15 m	45	170-01010

All dimensions in mm. Subject to technical changes. Minimum Order Quantity (MOQ) may differ from package content.

TYPE	Bundle Ø min.	Bundle Ø max.	Colour	Reel Length	Tools	Article-No.
Twist-In 05-5 m	4	5	Black (BK)	5 m	45	170-01011
Twist-In 08-5 m	5	8	Black (BK)	5 m	45	170-01012
Twist-In 13-5 m	10	13	Black (BK)	5 m	45	170-01013
Twist-In 19-2 m	16	19	Black (BK)	2 m	45	170-01014
Twist-In 25-2 m	19	25	Black (BK)	2 m	45	170-01015
Twist-In 29-2 m	25	29	Black (BK)	2 m	45	170-01016
Twist-In 32-2 m	29	32	Black (BK)	2 m	45	170-01017
Twist-In 38-2 m	32	38	Black (BK)	2 m	45	170-01018

All dimensions in mm. Subject to technical changes. Minimum Order Quantity (MOQ) may differ from package content.

Recommended Tools	
	45 HSG0
	570

For more information on toolings please refer to the Application Tooling chapter.



For product specific approvals and specifications please refer to the Appendix.



Add items to your watchlist!

www.HT.click/49-357

