


Low Profile Category 5e Euro Outlet



Low Profile Category 5e Euro Outlet (FJKjewh, FJKjewh#24)

This affordable outlet which easily performs to Category 5e TIA/EIA-568-C.2 at permanent link level, can be quickly and easily terminated and fits into most standard faceplates.

Features:

- Performs to Category 5e at permanent link level with good headroom
- Low profile design, shuttered front aperture protects against dust
- Fitted with industry standard Krone (LSA+) type IDC connections
- Compatible with most 'Euro-style' 86 x 86 faceplates
- 'Slip-in' label facility for port identification
- Integral cable tie point. Cable retention clip also supplied along with additional flexible cable tie facility.
- Available in individual polythene bags or in "bulk packs" of 24 without individual poly bags

Specifications:

- Weight: FJKjewh: 12g approx. FJKjewh#24: 288g approx.
- Dimensions (as packed): FJKjewh: 100 x 40 x 30mm FJKjewh#24: 260 x 220 x 90mm
- Colour: White (RAL 9003)

TUK Ltd, Unit 4, Wimbledon Stadium Business Centre, Riverside Road, London SW17 0BA

Materials:

IDC: IDC cap: ABS, UL 94-HB IDC Housing: PC + Glass fibre UL 94V-2 IDC Terminal: Tin plated phosphor bronze

RJ45 Jack: Housing: ABS UL 94-HB Contact bracket: PC 1250Y, UL 94V-0

RJ45 Jack Contact Material: Nickel plated phosphor bronze Finish: 50µ"/1.27 µm gold plating on plug contact area

- T568A and T568B wiring sticker
- Insertion force: 20N max.
- Retention strength: 7.7kg between jack and plug
- Operating temperature: -10°C to 60°C
- Suitable for 22-26 AWG stranded and solid wire with Krone (LSA+) type punch down tool.

Packaging:

FJKjewh: individually bagged, then bagged in 20s then in 100s *FJKjewh#24:* in box of 24 pcs, then in outer carton of 24 boxes

Commodity code: 84733020

EAN: FJKjewh: 5055386510440

FJKjewh#24: 5055386510457

Country of Origin: China

TUK Ltd, Unit 4, Wimbledon Stadium Business Centre, Riverside Road, London SW17 0BA




	•	
• • • • • • • • • • • • • • • • • • • •		

02/02/2023

TUK Ltd, Unit 4, Wimbledon Stadium Business Centre, Riverside Road, London SW17 0BA



ROHS Compliant



Specification :

Material :

- 1. IDC CAP : ABS, UL 94-HB.
- 2. IDC :
- 2-1. Housing : PC+Glass Fiber, UL 94V-2.
- 2-2. Terminal : Phosphor Bronze with Tin plated.
- 3. RJ45 Jack :
 - 3-1. Housing : ABS, UL 94-HB, with optional color.
- 3-2. Contact Bracket : PC 1250Y, UL 94V-0, Transparence color.
- 4. RJ45 Jack Contact :
 - 4-1. Material : Phosphor Bronze with Nickel plated.
 - 4-2. Finish : 50 micro-inch Gold plated on Plug contact area.
- 5. Cable holder : PP, UL 94V-2.
- 6. Modular Frame : ABS, UL 94-HB, with white color.
- 7. Identification :
- 7-1. I.D. Plate : Polycarbonate, UL 94V-0, Transparence color. 7-2. Paper.
- 8. Spring : SUS.
- 9. Dust Cover : ABS, UL 94-HB, with white color.
- 10. PCB : FR4, UL 94V-0.

Performance :

- a. T568A & T568B wiring sticker.
- b. Insertion force : 20N max. (IEC 60603-7-4)
- c. Retention strength : 7.7 kg between Jack and Plug.
- d. Operating temperature : -10° C to 60° C. (ISO/IEC 11801, ANSI/TIA 568 C.2)
- e. Life(mating cycles) :
 - *Jack : 750 cycles min. (ISO/IEC 11801, IEC 60603-7-4)
- *IDC : Suitable for 22-26 AWG stranded and solid wire, with Krone punch down tool.
- f. The Cat.5e channel transmission performance is in compliance with TIA/EIA 568 C.2 standard.

30/01/2023 TUK Ltd, Unit 4, Wimbledon Stadium Business Centre, Riverside Road, London, SW17 0BA

Tel: 020 8946 6688 Fax: 020 8879 7410 Email: sales@tuk.co.uk Website: www.tuk.co.uk

