

#### AMPLIMITE | AMPLIMITE Kit

TE Internal #: 5205980-4


D-Sub Locking & Mounting, Screw Retainer Kit, Screw Length 5.59

mm [.22 in], AMPLIMITE Kit

View on TE.com >



Connectors > D-Shaped Connectors > D-Sub Accessories > D-Sub Locking & Mounting











D-Shaped Connector Accessories: Screw Retainer Kit

Screw Length: 5.59 mm [.22 in]

#### **Features**

### **Product Type Features**

Product Type	Accessory
D-Shaped Connector Accessories	Screw Retainer Kit
Mechanical Attachment	
Screw Plating Material	Zinc
Screw Material	Carbon Steel
Screw Finish	Clear Chromate
Screw & Hole Thread Size	4-40
Screw Length	5.59 mm[.22 in]
Operation/Application	
For Use With	Metal Shell Connectors (HDE and HDP)
Packaging Features	
Packaging Quantity	1
Packaging Method	Bag

## **Product Compliance**

For compliance documentation, visit the product page on TE.com>



EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: JAN 2023 (233) SVHC > Threshold: Pb (.35% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

# Compatible Parts





Also in the Series | AMPLIMITE Kit





D-Sub Backshells & Clamps(135)



D-Sub Contact Accessories(1)




D-Sub Covers(3)



D-Sub Locking & Mounting(120)

# Customers Also Bought






TE Part #CN9929-000 SBP100743WE1



TE Part #1-745495-9 25 HDE MS RCPT,20-22,LEAD FREE



TE Part #3-644461-5
05P MTA156 CONN ASSY 18AWG LF











### **Documents**

# Product Drawings

**SCREW RETAINER KIT** 

English

### **CAD Files**

Customer View Model ENG\_CVM\_CVM\_5205980-4\_O.2d\_dxf.zip

English

3D PDF



3D

**Customer View Model** 

ENG\_CVM\_CVM\_5205980-4\_O.3d\_igs.zip

English

**Customer View Model** 

ENG\_CVM\_CVM\_5205980-4\_O.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

### Datasheets & Catalog Pages

**AMPLIMITE Subminiature D Connectors - Cable Connectors** 

English

AMPLIMITE Cable Connectors and Shielding Hardware Kits QRG

English

**Product Environmental Compliance** 

MD\_5205980-4\_0404201830\_dmtec

English

MD\_5205980-4\_0404201830\_dmtec

English

**Instruction Sheets** 

Instruction Sheet (U.S.)

English