

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2196551111

Status:

Active

Overview:

Off-the-Shelf Pre-Crimped Leads

Description:

Pre-Crimped Lead Micro-One Female-to-Pigtail, Matte Tin Plating, 75.00mm Length, 24 AWG, Black

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Datasheet (PDF)

General

Product Family

Cable Assemblies

Series

219655

Application

Signal, Wire-to-Board

Assembly Configuration

Pre-crimped Lead Only

Connector to Connector

Micro-One-to-Pigtail

Overview

Off-the-Shelf Pre-Crimped Leads

Product Name

Micro-One

Taxonomy

Power and Signal Cable Assembl

UPC

195842803879

Physical

Cable Length

75.00mm

Circuits (Loaded)

1

Color - Resin

Black

Gender

Female-Pigtail

Material - Metal

Copper Alloy

Material - Plating Mating

Matte Tin

Net Weight

0.383/g

Packaging Type

Bag

Plating min - Mating

0.900µm

Plating min - Termination

0.900µm

Single Ended

Yes

Termination Interface: Style

Crimp or Compression

Wire Insulation Diameter

1.10-1.60mm

Wire Size AWG

24

Wire/Cable Type

UL 1569

Electrical

Current - Maximum per Contact

4.0A

Voltage - Maximum

250V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Sales Drawing2196551121-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained per - D(2022)9120-DC (17 Jan 2023)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

219655 Series

Use With

Micro-One Receptacle Housing [205979](#) , [212724](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION