

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2196552102

Status:

Active

Overview:

Off-the-Shelf Pre-Crimped Leads

Description:

Pre-Crimped Lead Micro-One Female-to-Pigtail, Matte Tin Plating, 150.00mm Length, 26 AWG, Red



Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Datasheet \(PDF\)](#)

General	
Product Family	Cable Assemblies
Series	219655
Application	Signal, Wire-to-Board
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Micro-One-to-Pigtail
Overview	Off-the-Shelf Pre-Crimped Leads
Product Name	Micro-One
Taxonomy	Power and Signal Cable Assembl
UPC	195842803985
Physical	
Cable Length	150.00mm
Circuits (Loaded)	1
Color - Resin	Red
Gender	Female-Pigtail
Material - Metal	Copper Alloy
Material - Plating Mating	Matte Tin
Net Weight	0.496/g
Packaging Type	Bag
Plating min - Mating	0.900µm
Plating min - Termination	0.900µm
Single Ended	Yes
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.88-1.30mm
Wire Size AWG	26
Wire/Cable Type	UL 1569
Electrical	
Current - Maximum per Contact	3.5A
Voltage - Maximum	250V AC (RMS)/DC
Material Info	
Reference - Drawing Numbers	
Sales Drawing	2196551101-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained per -
D(2022)9120-DC (17
Jan 2023)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

219655 Series

Use With

Micro-One Receptacle Housing 205979 ,
212724

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION