

## Data Sheet

### Microwave Cable Assemblies

PMASF526S/11PC35/11PC35/24in Part No.: 85185119

### Main characteristics

SUCOFLEX 526S microwave cable assemblies set a new measurement standard through 26.5 GHz. Absolute phase matched +/- 1ps



### Product configuration

Cable Type	SUCOFLEX 526S
Lenght	610.0 mm 24.0 in REF to REF

	Type	Series		
Connector A	SF_11_PC35-501	3.5 mm	straight	plug
Connector B	SF_11_PC35-501	3.5 mm	straight	plug

### Technical data

#### Electrical data

Impedance	50.0 Ω
Operating Frequency max	26.5 GHz
Min. Return Loss	19.0 dB VSWR 1.253
Max. Insertion Loss	1.18 dB
Signal Delay	4.3 ns/m
Propagation Velocity	77.0 %
Screen Effectiveness	≥ 90.0 dB 26.5 GHz
Amplitude stability vs.Flex[±]	0.05 dB
Phase Stab vs.Flexure	0.2 °/GHz

#### Mechanical data

Cable Diameter max	7.7 mm
Minimum Bending Radius Static	25.4 mm
Weight	0.11 kg

#### Environmental data

Operation Temperature Range	-55.0 °C ... 125.0 °C
-----------------------------	-----------------------

### Additional information

Marketing Information	Absolute phase matched +/- 1ps
-----------------------	--------------------------------