



## BlackFin CT-2504CH Crimp Head

CT-2504CH

Crimp Head for use with Panduit CT-2500 , CT-2500/E, CT-2500/L and CT-2500/LE crimp tools. Crimps Panduit #8-6 AWG single wire ferrules and Panduit #10 AWG twin wire ferrules. Square crimp profile.

### Specifications

|                         |   |
|-------------------------|---|
| Compatible Connector    | Loose Piece F and FSD series Ferrules                             |
| Tool Type               | Die Type  |
| Maximum Wire Size (AWG) | #6  |
| Minimum Wire Size (AWG) | #8  |
| Sub Brand               | BlackFin  |
| For Use With            | CT-2500 , CT-2500/E, CT-2500/L and CT-2500/LE crimp tools         |
| Overall Height (In.)    | 2   |
| Overall Height (mm)     | 50  |
| Overall Width (In.)     | 1   |
| Overall Width (mm)      | 25  |
| Product Type            | Crimp Head  |
| Weight (Kg)             | 0.4   |
| Weight (lb)             | 0.92  |
| Crimp Profile           | Square  |
| Base Material           | Steel   |
| Application             | CT-2500, CT-2500/E and CT-2500/L, CT-2500/LE Crimp Tools          |
| Color                   | Black   |
| Part Features           | Self-adjusting crimp die for Insulated and noninsulated ferrules. |

### Packaging Detail

|                       |             |
|-----------------------|-------------|
| UPC                   | 61305618128 |
| Std. Pkg. Qty.        | 1           |
| Std. Pkg. Volume (cf) | 0.0366      |
| Std. Ctn. Qty.        | 0           |
| Std. Ctn. Volume (cf) | 0.0000      |