



Contour Crimp™ CT-1090 Ferrule Crimp Tool

CT-1090

Controlled Cycle Ferrule Crimp tool with square profile for #26 - 10 AWG (0.14-6.0mm²) insulated and non-insulated single wire ferrules and #22 - 12 AWG (0.05 - 4.0mm²) insulated twin ferrules.

Specifications

Compatible Connector	Loose Piece F, FSD, FSDX, FSDXL, and FTD series Ferrules
Maximum Wire Size (AWG)	#10
Minimum Wire Size (AWG)	#26
Sub Brand	Contour Crimp™
Maximum Wire Size (mm ²)	0.14
Minimum Wire Size (mm ²)	6
Overall Height (In.)	0.12
Overall Height (mm)	3.1
Overall Length (In.)	0.34
Overall Length (mm)	8.7
Overall Width (In.)	0.78
Overall Width (mm)	20
Product Type	Ferrule Crimp Tool
Weight (Kg)	0.5
Weight (lb)	1.12
Crimp Profile	Trapezoid
Base Material	Steel
Application	Pan-Term Ferrules
Color	Black

Packaging Detail

UPC	61305618124
Std. Pkg. Qty.	1
Std. Pkg. Volume (cf)	0.0626
Std. Ctn. Qty.	0
Std. Ctn. Volume (cf)	0.0000