


Applications	General use
Feature	VHF Chokes
Series	VHF chokes
Status	Production
Brand	EPCOS



Size	
Design	Axial
Diameter(D)	7.50mm Max.
Length(L)	26.00mm Max.

Electrical Characteristics	
Inductance	7 μ H \pm 20% at 1MHz
Rated Current	5A
DC Resistance	20m Ω \pm 20%
Q [Min.]	
Resonance Frequency	180MHz \pm 30%

Other	
Operating Temp. Range	-55 to 125°C
Soldering Method	Wave (Flow)
Packing	Axial Taping Reel
Package Quantity	1000pcs
Approx. Weight	3.6g

! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.