Mains Power Cords India to IEC C19

multicomp PRO




RoHS Compliant

Specifications

Connector to Connector: Mains Plug, India to IEC 60320 C19

Current Rating : 16A
Cable Length : 2m
Jacket Colour : Black

Diagram



Notes:

- 1. Cable: The cord shall comply with IS694.
- 2. Plug: The molded plug shall comply With IS1293.
- 3. Connector: The connector shall comply with IEC60320-1 standard (C19 connector).
- 4. The product shall be tested 100% for all safety electrical items.
- 5. Colour: Black

Item	Description	Qty.
1	BIS Circular 3 × 1.50mm², Black	
2	Molded plug, 16A/250V	1
3	Molded Connector, 16A/250V	'
4	Mini tie	

Part Number Table

Description	Part Number
Mains Power Cord, India to IEC C19, 250V, 16A, Black, 2m	GW-151712

Dimensions: Millimetres

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

