

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0988171030**
Status: **Active**
Overview: NSCC - New Standard Casing Contact
Description: NSCC Single Part, Unsealed, 1.50mm, Female Housing, 3.33mm Pitch NSCC, Wire-to-Wire, 3 Circuits, White

Documents:

3D Model	Application Specification 988210001-PS-CH-001 (PDF)
Drawing (PDF)	Packaging Specification PK-31301-635-001 (PDF)
Product Specification PS-98821-001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification 988210001-AS-CH-001 (PDF)	

Application tooling part link

Application Tooling Part Link 63813-3800

General

Product Family	Crimp Housings
Series	98817
Application	Power, Wire-to-Wire
Overview	NSCC - New Standard Casing Contact
Product Name	NSCC
Taxonomy	Connector Housings
UPC	822348760916

Physical

Breakaway	No
Circuits (maximum)	3
Circuits Detail	3 x 1.5mm female terminals
Color - Resin	White
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	2.150/g
Number of Rows	1
Packaging Type	Carton
Panel Mount	No
Pitch - Mating Interface	3.33mm
Pitch - Termination Interface	3.33mm
Polarized to Mating Part	Yes
Ports	1
Temperature Range - Operating	-40° to +100°C

Electrical

Current - Maximum per Contact 10.0A

Solder Process Data


Lead-freeProcess Capability N/A

Material Info

Engineering Number 010109329

Reference - Drawing Numbers

Application Specification 988210001-AS-CH-001, 988210001-PS-CH-001
 Packaging Specification PK-31301-635-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[98817 Series](#)

Mates With

[988221030 Male Receptacle Housing](#)

Use With

Female Terminal NSCC [988971109](#) , [988971119](#) , [988971129](#) or FCI Female Terminal 1.5 Sicma 3

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Extractor Tool for Unsealed Receptacle Connectors	638133800
---	---------------------------

This document was generated on 02/03/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION