

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [5051106891](#)  
**Status:** **Active**  
**Overview:** [Easy-On FFC FPC Connectors](#)  
**Description:** Easy-On FFC/FPC Connector 0.50mm Pitch, FD19 Series, Right-Angle, Bottom Contact, 1.90mm Height, 68 Circuits, Gold over Nickel Plating

**Documents:**

|                                                               |                                                      |
|---------------------------------------------------------------|------------------------------------------------------|
| <a href="#">Drawing (PDF)</a>                                 | <a href="#">Datasheet (PDF)</a>                      |
| <a href="#">3D Model (PDF)</a>                                | <a href="#">Product Guide (PDF)</a>                  |
| <a href="#">3D Model</a>                                      | <a href="#">RoHS Certificate of Compliance (PDF)</a> |
| <a href="#">Product Specification 5051100000-PS-000 (PDF)</a> | <a href="#">Reference Guide (PDF)</a>                |
| <a href="#">Packaging Specification 5051109200-200 (PDF)</a>  |                                                      |

**General**

|                |                                            |
|----------------|--------------------------------------------|
| Product Family | FFC/FPC Connectors                         |
| Series         | <a href="#">505110</a>                     |
| Comments       | Black Actuator                             |
| Overview       | <a href="#">Easy-On FFC FPC Connectors</a> |
| Product Name   | Easy-On                                    |
| Series Name    | FD19                                       |
| Taxonomy       | FFC / FPC Connectors                       |
| UPC            | 889056229371                               |

**Physical**


|                                |                        |
|--------------------------------|------------------------|
| Actuator Type                  | Front Flip             |
| Circuits (Loaded)              | 68                     |
| Circuits (maximum)             | 68                     |
| Color - Resin                  | Beige                  |
| Contact Position               | Bottom                 |
| Durability (mating cycles max) | 20                     |
| Mated Height                   | 1.90mm                 |
| Material - Metal               | Phosphor Bronze        |
| Material - Plating Mating      | Gold                   |
| Material - Plating Termination | Gold                   |
| Material - Resin               | Liquid Crystal Polymer |
| Net Weight                     | 519.680/mg             |
| Number of Rows                 | 1                      |
| Orientation                    | Right Angle            |
| PCB Locator                    | No                     |
| PCB Mounting                   | Surface Mount          |
| PCB Retention                  | Yes                    |
| Packaging Type                 | Embossed Tape on Reel  |
| Pitch - Mating Interface       | 0.50mm                 |
| Pitch - Termination Interface  | 0.50mm                 |
| Plating min - Mating           | 0.051µm                |
| Plating min - Termination      | 0.051µm                |
| Polarized to PCB               | Yes                    |
| Stackable                      | No                     |
| Temperature Range - Operating  | -40° to +105°C         |
| Wire/Cable Type                | FFC/FPC                |

**Electrical**

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 0.5A |
| Voltage - Maximum             | 50V  |

**Material Info**

**Reference - Drawing Numbers**



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained per -  
D(2022)9120-DC (17  
Jan 2023)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[505110 Series](#)

Packaging Specification  
Product Specification  
Sales Drawing

5051109200-200  
5051100000-PS-000  
5051100000-SD-000, 5051101000-SD-000

This document was generated on 03/21/2023

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**